TEC Controller / Peltier Driver up to ±10 A / up to ±21V

TEC-1161

HW v1.10

Two Channel OEM TEC Controller



Description:

The TEC-1161 is a specialized TEC Controller / power supply able to precision-drive two Peltier elements.

Each channel features a true bipolar DC current source for cooling / heating, six temperature monitoring inputs (2x high resolution, 4x low resolution) and intelligent PID control with auto tuning. The TEC-1161 is fully digitally controlled, it's hard- and firmware offer numerous communication and safety options.

The included PC-Software allows configuration, control, monitoring and live diagnosis of the TEC Controller via USB and RS485. All parameters are saved to non-volatile memory. Saving can be disabled for bus operation.

For the most straightforward applications, only a power supply, Peltier elements and at least one temperature sensor need to be connected to the TEC-1161. After power-up the unit will operate according to preconfigured values. (In stand-alone mode no control interface is needed.)

The TEC-1161 can handle either Pt100, Pt1000, NTC or Voltage temperature probes. For highest precision and stability applications a Pt100 / 4-wire input configuration is recommended. Analog measurement circuit is factory calibrated.

Auxiliary temperature inputs allow the connection of NTC probes that are located on the heat sinks of the Peltier elements. This additional data is used to compensate for parasitic thermal conduction of Peltier elements. Also, it allows the control of external heat sink cooling fans.

The heating and cooling power is optimized by proprietary thermal management routines based on power balance models (for Peltier elements and resistive heaters).

The TEC-1161 two independent channels may also be operated in parallel, to either drive two individual or one common load (current doubling).

Further functionality includes: Smooth temperature ramping, thermal stability indication and auto gain (NTC probes). The PC-Software allows data logging and configuration import/export.

Features

Input Characteristics:

DC Input Voltage: 5 to 24 V

Output Characteristics:

Voltage: up to ± 21 VCurrent: up to ± 10 A

Main Features:

- Temperature Sensor Types: Pt100, Pt1000, NTC, Voltage
- Temperature Precision / Stability: <0.01 °C
- Temperature Control & Measurement Frequency: 1 Hz, 10 Hz, 90 Hz
- Communication bus compatible
- Configuration and monitoring with Service Software
- PCB mountable version available

Operation Modes:

- Stand-alone operation
- Remote-controlled over USB, CAN, RS485, I/O
- Script-controlled over lookup table (thermal cycling)

Driver Modes:

- DC power supply (bipolar)
- Temperature control: PID settings, auto tuning, optional cool/heat-only or resistor heating modes

Data Interfaces:

- USB
- RS485
- CAN

General Purpose I/O Features:

- Configurable as input to control TEC-1161 (Enable, Temperature up / down etc.)
- Configurable as output to monitor TEC-1161 (Error Indication, Temperature Stable Indication etc.)

Special Requirements / More Information:

Please contact us for additional information or customization.

Important Note:

The following features will be activated with an incoming firmware update, but are not yet useable:

- All CAN Interfaces
- GPIO9 and GPIO10
- Low Resolution temp. measurement 3 and 4




TEC Controller / Peltier Driver up to ±10 A / up to ±21V


TEC-1161 HW v1.10


Absolute Maximum	Ratings
Supply voltage (DC)	25.5V


Operating Ratings	
Temperature	-40 – 90°C
Humidity	5-95%, non-condensing

Operating Characteristics











Standard or Extended Device Temperature Mode can be set as software setting. The right Diagram shows the situation with an external 3.3Ω resistor (4A Model) or a 1.65Ω resistor (10A Model). No forced air flow was present.

Efficiency





The Efficiency measurements were done at 21V output voltage and a device temperature of 60°C. The ambient temperature was 23°C, no forced air flow was present.

TEC Controller / Peltier Driver up to ±10 A / up to ±21V

TEC-1161

Document Number: 5231C (24 July 2020)

HW v1.10

Electrical Characteristics 4A Model

Unless otherwise noted: T_A = 25°C, U_{IN} = 24 V, R_{load} = 3.3 Ω

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units				
DC Power S	OC Power Supply Input:									
U _{IN}	Supply voltage		4.9		24	V				
U _{IN} Ripple	Ripple tolerance	UIN never below UIN min or above UIN max			300	mV_{PP}				
Output:										
Гоит	Bipolar current swing				±4	Α				
Uouт	Bipolar voltage swing	U _{OUT} is maximum ~0.9 ⋅ U _{IN} ; See diagram			±21	V				
Uout Ripple	Voltage ripple	@ 4 A			100	mV_{PP}				
System Cha	aracteristics:									
η _{50%}	Power efficiency	@ 50% load (10.5V, 4A)		94		%				
η100%	Power efficiency	@ 100% load (21V, 4A)		96		%				
Output Mon	itoring (IOUT Resolution	is 1.46mA; Uo∪⊤ Resolution is 6.1mV)								
louт Read	Precision	@ 3.8 A		1	5	%				
Uout Read	Precision	@ 15.0 V		1	3	%				

Electrical Characteristics 10A Model

Unless otherwise noted: T_A = 25°C, U_{IN} = 24 V, R_{load} = 1.65 Ω

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units			
DC Power S	DC Power Supply Input:								
U _{IN}	Supply voltage		4.9		24	V			
U _{IN} Ripple	Ripple tolerance	UIN never below UIN min or above UIN max			300	mV_{PP}			
Output:									
lout	Bipolar current swing				±10	Α			
U _{OUT}	Bipolar voltage swing	U _{OUT} is maximum ~0.9 ⋅ U _{IN} ; See diagram			±21	V			
U _{OUT} Ripple	Voltage ripple	@ 10 A			350	mV_{PP}			
System Cha	aracteristics:								
η50%	Power efficiency	@ 50% load (10.5V, 10A)		93		%			
η100%	Power efficiency	@ 100% load (21V, 10A)		95		%			
Output Mon	itoring (IOUT Resolution	is 3.5 mA; U _{OUT} Resolution is 6.1mV)							
louт Read	Precision	@ 9.8 A		1	5	%			
Uout Read	Precision	@ 15.0 V		1	3	%			

Output Safety Characteristics

Unless otherwise noted: $T_A = 25$ °C, $U_{IN} = 12 \text{ V}$

Symbol	Parameter	Test Conditions / Hints	Min	Тур	Max	Units				
Output Sta	Output Stage Protection Delays:									
toff Short circuit		Full load condition		10	30	μS				
toff Power system limits		Current and voltage limits			200	μS				
	ge Current Supervis nd OUT- currents differ too	ion: much, an error is generated)								
IOUT_DIFF	Error threshold	·		120		mΑ				

High Resolution Temperature Measurement Characteristics (NTC Probes)

NTC thermistor resistive input characteristics translate into temperature ranges valid for only one type of NTC probe. Below example is given in the case of an NTC $B_{25/100}$ 3988K R_{25} 10k temperature sensor.

Symbol	Parameter	Test Conditions / Hints	Min	Тур	Max	Units
Б	ADC Auto Gain		73		1M	Ω
RHR, RANGE	PGA = 1 or 8 or 32		1	194.3 to -55.5		°C

TEC Controller / Peltier Driver up to ±10 A / up to ±21V

TEC-1161

HW v1.10

ROBJ, RANGE is resistance range of the NTC sensor

High Resolution Temperature Measurement Characteristics (Pt100 and Pt1000 Probes)

Measurement configuration = 23 bit / 4-wire / unshielded cable <50 mm

Symbol	Parameter	Test Conditions / Hints	Min	Тур	Max	Units
Tobj, range	Range	Range is extendable upon request Extended measurement range is -193°C +787°C	-220		+200	°C
T _{OBJ, PREC}	Precision	(EN 60751 / IEC 751)		0.005		°C
T _{OBJ} , COEFF	Temp. Coefficient	Relative to device temperature			1.6m	°C/K
T _{OBJ, NOISE}	Value Noise	Reference measurement fluctuations while output stage operating @70% load		0.005		°C
T _{OBJ} , REP	Repeatability	Repeated measurements of reference resistors after up to 3 days		0.008		°C

High Resolution Temperature Monitoring Configuration (Voltage Measurement VIN1)

Sensors with linear Voltage/Temperature output.

Symbol	Parameter	Test Conditions / Hints	Min	Тур	Max	Units
VSENS, DIFF	Range	Differential Input voltage Temperature range depends on sensor used	-2.039		2.039	V
Vobjux, abs	Range	Absolute Input voltage	-0.1		5.1	V

Low Resolution Temperature Measurement Characteristics (NTC only)

 $T_A = 25$ °C, measurement configuration = 12 bit / 2-wire / unshielded cable <50 mm, °T probe = NTC B_{25/100} 3988K R₂₅ 10k

Symbol	Parameter	Test Conditions / Hints	Min	Тур	Max	Units
В	Dongo		50		49781	Ω
KLR, RANGE	Range	Corresponding temperature range		214 to -8.1		°C

General Purpose Digital I/O Characteristics (GPIO1 ... GPIO10)

Unless otherwise noted: $T_A = 25^{\circ}C$


Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Input Char	acteristics:					
U _{IH}	Logic high input threshold		2.38			V
U _{IL}	Logic low input threshold				0.93	V
U _{IMAX}	Maximum input voltage		-0.5		5.5	V
Output Ch (Microprocess	aracteristics:					
Uон	Logic high output voltage	Output current 8mA	2.8		3.3	V
Uol	Logic low output voltage	Input current 8mA			0.4	V
Zouт	Output Impedance		110	120	150	Ω
louт	Output Sink or Source Current			±8	±20	mA
ESD Prote	ction:					
(Between Pro	cessor and Connector)					
UPP	ESD discharge	IEC61000-4-2		18		kV
	Series resistance		85	100	115	Ω

Auxiliary Connector X5 Power Supply Output Characteristics

Unless otherwise noted: $T_A = 25^{\circ}C$

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units				
Input Characteristics:										
U _{оит}	Output voltage	Output current 50mA	4.4	4.5	5	V				
louт	Output current		0	150	200	mA				
U _{IMAX}	Maximum input voltage		-0.5		5.5	V				

Pin Configuration Screw Connectors TOP View



Matching Receptacles for the PIN Configuration

The following receptacles can be used for the TEC-1161 in the -PIN Configuration: Manufacturer: MILL-MAX NANUFACTURING Part Number: 801-43-050-10-001000

The receptacles need to be broken up into the appropriate length.


Screw Connector Specifications X1 and X2

Parameter	Min	Тур	Max	Units
Wire Size (Mechanical Limit, current carrying capacity not considered)	0.05		2.5	mm ²
Torque		0.5	0.6	Nm
Stripping Length	0.5		0.6	mm

Screw Connector Specifications X3, X4 and X8


Parameter	Min	Тур	Max	Units
Wire Size (Mechanical Limit, current carrying capacity not considered)	0.05		1	mm ²
Torque		0.1		Nm
Stripping Length		0.5		mm

Temperature Sensor Connection X4 and X8




The Jumpers are used for the 2/4 Wire configuration. For the values of RS and RP please refer to the TEC-Controller User Manual.

Pin Configuration Pinheader Connectors TOP View



Pin Configuration Auxiliary IO Connector X5




Mini USB Connector X6

The Mini USB Connector X6 can be used to communicate with the TEC-Controller using the meCom communications protocol or the Service Software. It is electrically isolated.

Display Connector X9

The Connector X9 can be used to connect one of the OLED Displays available from Meerstetter (DPY1113, DPY1114 or DPI1115)

Temperature Sensor Connection X4 and X8



Low Resolution Temperature


[NTC]


HW v1.10

TEC Controller / Peltier Driver up to ±10 A / up to ±21V

Dimensions

Top View





The holes marked in red are used to mount the alluminium Baseplate for the 10A version and are therefore not available for mounting purposes in this version.

HW v1.10

Operation-Modes / Theory of Operation

The TEC-1161 is an OEM precision TEC Controller that is available with Screw Terminals or as a PCB mountable device. Its basic operation status is visually indicated by on-board green and red LEDs and their blinking pattern.



-SCREW Screw terminal equipped Version




-PIN PCB mountable Version

Status information can be polled at any time by industry standard RS485 connection or by USB (see box below). The TEC-1161 can also operate in a remotely controlled manner, with parameters adjusted on the fly. The TEC-Controller has Scripting capability by sequential lookup table read-out.

Configured as a DC power-supply, the TEC-1161 can handle current and voltage settings. In the remote-control case, temperature data may be passed on to be processed by the host.

Configurable parameters further include sensor linearization (Pt100 / Pt1000) and Steinhart-Hart modeling (NTC), temperature acquisition hardware calibration, Peltier element modeling, PID controller auto tuning, nominal temperature ramping, current, voltage and temperature limits, error thresholds, etc. Please refer to the TEC Controller User Manual (Document 5216) for further information.

TEC-1161 Ordering Information, Hardware Configuration



High Resolution Sensor Type:

Thermocouple: To use our TEC Controller with thermocouples type K, you need a TCI-1181 in addition to the TEC Controller with a VIN1 Object Sensor Type configuration.

Meerstetter Engineering GmbH Schulhausgasse 12 3113 Rubigen, Switzerland



Phone: +41 31 529 21 00 Email: contact@meerstetter.ch Website: www.meerstetter.ch

Meerstetter Engineering GmbH (ME) reserves the right to make changes without further notice to the product described herein. Information furnished by ME is believed to be accurate and reliable. However typical parameters can vary depending on the application and actual performance may vary over time. All operating parameters must be validated by the customer under actual application conditions.